



Product Code

9700/RA6

Electrical Actuator
10Nm 230V 50/60Hz

GO GREEN

BY THE MATHS WE RECOVERED

POLYHEDRA

CLASSIC

Product use

Actuators can be assembled, using suitable flanged adaptors, to 2-ways ball valves and to manual 3-ways ball valves. They are assembled directly on the motorized 3-ways ball valves. Once this coupling has been performed, the valve can be opened or closed remotely. Alternatively, the actuator can be excluded and the valve can be operated manually.

Castel manufacturers actuator with a variety of operational characteristics: they are manufactured with a synthetic, self-extinguishing housing that covers the motor, the control and cut-out electronics based on the gear reducer torque and the self centring fixing system of the valve rod.

In the event of a power outage to the actuator, the gear reducer can be disengaged using the specific lever, to permit manual use of the valve.

Furthermore, auxiliary contacts for switching are available for remote control of the valve status.

Product details

Tension [V]	230
Fréquence [Hz]	50/60
Puissance [W]	2,9
Degrè de protection	IP 43
Angle de rotation	90°

Couple [Nm]	10
Durée de course [sec]	60
Température ambiante [°C] min.	-20
Température ambiante [°C] max.	+50
Adaptée puor vanne à boisseau	voir les raccords indiqués dans le tableau SCHÉMA DE COUPLAGE
Emballage	1

Notes

- (1) Connexions électriques : sortie à contacts à 2 points (ouvert/fermé) ou sortie progressive (0 ÷ 10V)
- (2) Connexions électriques : sortie à contacts à 2 points (ouvert/fermé)
- (3) Connexions électriques : sortie progressive (0 ÷ 10V)